

Setup in 9 steps

broncolor *scope D50*

Operating instructions

- 1 Place a uniform and non-reflecting underlay, e.g. on a table.
- 2 You can either position the Scope D50 on a level surface (2a) or you can mount it on a sturdy stand (2b). In the former case, you can either screw on the 4 adjusting feet alone, or combine them with the 4 supporting feet. Place the Scope D50 upside down on a level surface in order to mount the feet.
- 3 Now fix the camera mount to the Scope D50's top by means of the two integrated screws.
- 4 Attach your camera to the camera mount. Please use a macro lens. The lens must not be inserted deeper than 7 cm (2.76") in order to prevent shadowing on the object.
- 5 Connect the camera and the Scope D50 with the spiral sync cable.
- 6 Connect Scope D50 with the mains power supply using the provided mains adapter and mains cable (start with the plug connection on Scope D50's control panel). The display lights up and the system is being started.

⚠ The power plug serves to disconnect Scope D50 from the mains; therefore, it should be easily accessible at all times.

- 7 Place the object you wish to capture underneath the Scope D50 and centre it. Ideally, the surface of the object should be placed flush with the lower edge of Scope D50. You can adjust the device's height by means of the 4 screwable supporting feet, or by adjusting the stand's height, respectively.
- 8 Always press the round key at the bottom of the operating panel before unplugging the cable in order to switch off the operating system. Please wait until the display turns completely black (approx. 7 seconds), then unplug.
- 9 Please follow the next steps as described in this document (please see overleaf) in order to create the first capture and transfer the images to the computer.

⚠ Do not reach into the Scope, the LED could be damaged.

⚠ Switch off the LED prior to placing/positioning the object.



broncolor.swiss/scope
truvvis.ch/authentica/docs

Scope of delivery



Minimum system requirements

Lenses

Fixed focal length macro lenses (also tilt-shift lenses) with a focal length between 50 mm (1.97") and 105 mm (4.13"). Basically, also other lenses are possible as long as the maximum angle of view is not exceeded.

Max. depth of insertion of the lens

Maximum depth of insertion: 7 cm (2.76"). The max. depth of insertion, measured from the outer edge of the Scope D50, should not be exceeded in order to avoid a shadow of the lens on the object.

Max. angle of view

80° with a depth of insertion of 0 cm (0")

115° with a depth of insertion of 7 cm (2.76")

The max. angle of view should not be exceeded in order to avoid lens flares.

Object size and distances

Max. diameter of the object: 32 cm (12.60")

Max. length of the edge of a square object:
22 cm (8.66")

Max. distance lower edge Scope D50 to surface of the object: 15 cm (5.90")

Variable height due to combination of supporting and adjustable feet: 1.5 - 6 cm (0.59" - 2.36") and 10.5 - 15 cm (4.13" - 5.90")

Hardware and operating system

PC: Windows 10

Mac: Mac OS 10.11

RAM: 4 GB

Processor speed: 2 GHz

Free disk space: 500 MB

(for the setup of the programme)

Notice for UK customers (wireless LAN and defined Support Period)

Notice for UK customers:
This device can be configured to connect to a wireless LAN network.
Please configure this product to connect to secured infrastructure.
Do not use the configuration mode for normal operation.
Reports about Security Vulnerabilities: support@broncolor.swiss
Reaction time: 30 days

Form of the object

In general, objects with a slighter bend of the surface are more suitable than those with a strong bend. The latter could produce a shadow on the object itself.

Recommendation

Ideally, the surface of the object should be placed flush with the lower edge of Scope D50.

Interaction of Scope D50 & camera

1. Camera settings

White balance: If your camera offers to choose the colour temperature directly select a colour temperature of 5000 K. If this option is not available choose the normal day-light presets.

Image quality: RAW or TIFF (sRGB).

Exposure: We generally recommend ISO sensitivities of maximally 800 together with a shutter speed of 1/60 s to 1/80 s and an aperture of 11 to 14.

Interval shooting: If your camera offers this option set the number of intervals to 48, the length of the interval to 1 second and choose one shot per interval. If you are using a capture software you might have to choose longer intervals to make sure the images can be transferred to your computer in time.

Note

If your camera has an orientation sensor switch it off. If it is not switched off some images might be rotated since the camera is placed horizontally on the Scope D50.

UK Defined Support Period: 2 years after date of sale, only applicable to products sold in the UK (except Northern Ireland) on or after April 29th, 2024
Manufacturer's name: Bron Elektronik AG
Manufacturer's address: Hagmatstrasse 7, 4123 Allschwil, Switzerland

2. Acquisition

- The menu item "SETUP" allows to adjust the brightness of the LED. "ALL" alters the brightness of all 48 LED simultaneously. Use this modelling light function to focus the lens / to control the depth of field. "SINGLE" controls the brightness of the actual image capturing process (thereby, for every picture taken, an alternating LED is being activated).
- In the following, press the button "SEQUENCE" in the main menu. Press "START". One LED lights up.
- You can now start the acquisition process by using your camera's interval shooting option (48 pictures) or an image capture software of your choice. (In principle, you can also trigger the camera 48 times by hand but this is not recommended since it might cause blurring of the images and slight changes of the camera position.)
- For each image another LED is lit in the Scope D50.
- Make sure there are no other light sources lighting the object by checking your camera's live view. With only a small amount of ambient light you should still obtain reasonable results. If required you can use the included light protection elements:
 - light protection wrap
 - light protection collar (on the lens).

3. Prepare images for Authentica Creator

Transfer the acquired images from the camera to your computer.

- Open all images simultaneously in Photoshop or any other image processing programme.
- Select all images and adjust the brightness and colour temperature.
- Apply corrections for chromatic aberration and lens profile of your camera.
- Crop a rectangular selection which contains the object
- Create a new folder and save the images as TIFF images using sRGB as colour space.
- You can use a colour depth of 16 or 8 bit for the TIFF images.

Note

Make sure you only crop rectangular sections and don't rotate the RAW or TIFF images. You will have the possibility to cut non rectangular sections and apply rotation in Authentica Creator once the digital material is created.

4. Installing Authentica Creator

In order to install and unlock the Authentica Creator software, please follow the instructions as stated in the provided license card.

Note

Detailed information on the use of Authentica Creator can be found on: truvis.ch/authentica/docs
Please note the enclosed safety instructions or find them on: broncolor.swiss/support/downloads

broncolor

Operating instructions



Technical data

| | |
|------------------------|--|
| Dimensions (L x W x H) | 59 x 50 x 48 cm (23.2" x 19.7" x 18.9") |
| Weight | 9.96 kg (21.96 lbs) (Scope including camera mount, stand holder, adjustable and supporting feet) |
| Materials Supply | Steel, aluminium, ABS plastic |
| voltage Power input | 85...260 VAC, 47...63 Hz < 100 W |
| Ambient temperature | 0 to 50 °C (32 to 122 °F) |
| Ambient humidity | 0 to 85 % non-condensing |
| Storage temperature | -10 to 70 °C (14 to 158 °F) |
| Light | Scope D50 (82.110.00) 48 x white LED, colour temperature 5000 K ± 75 K, 1500 lm max., CRI > 90 Scope D50 UV / IR (82.130.00) 48 x white LED, colour temperature 5000 K ± 75 K, 1500 lm max., CRI > 90 48 x LED UV (385 - 395 nm), max. 1600 mW 48 x LED IR (920 - 960 nm), max. 1600 mW |
| WiFi | 802.11b/g/n |
| Display / Operation | 2.8" touch display, 240 x 320 pixel, 262144 colours / Touch control |
| Protection | IP20 |



Note safety instructions!